

Ultrasonic Flow Meter PCE-TDS 100HS



Ultrasonic Flow Meter PCE-TDS 100HS Measures liquid flow velocity in pipes and tubes with a diameter of 20 ... 108 mm / \approx 3/4 ... 4 in

This is a portable handheld clamp-on ultrasonic flow meter used for non-invasive, unobstructed and highly accurate measurements of the flow velocity of liquids in metal, plastic and rubber **pipes and tubes with a diameter of 20 ... 108 mm / approx. 3/4 ... 4 in**. Ideal for use in oil and gas, water and wastewater, chemical, food and beverage, pharmaceutical, metals and mining, pulp and paper, power and heating, ventilation, air conditioning and refrigeration (HVACR) industries, this ultrasonic flow meter features user-friendly velcro-strap clamps that allow for quick and easy repositioning of the electroacoustic transducers.

Measurable liquids include: acetate, acetone, alcohol, ammonia, aniline, benzene, butyrate, chloroform, ethanol, ethyl alcohol, ethyl ether, ethylene glycol, freon R 12, petrol, glycerin, glycol, isobutanol, isobutane, isopentane, kerosene, linseed oil, methanol, methyl alcohol, engine oil, diesel oil, olive oil, peanut oil, paraffin oil, pentane, petroleum, 1-propanol, coolant, lubricating oil, silicone oil, transformer oil, trichlorethylene, 1, 1, 1 - trichloroethane, turpentine, distilled water and sea water.

Calculation of flow velocity according to the transit-time principle follows the equation:

$$v = \frac{(T_2 - T_1)}{T_1 T_2} * \frac{L}{2cos\alpha}$$

v= measured velocity

T1 = run time of the ultrasonic signal in the flow direction

T2 = run time of the ultrasonic signal against the flow direction

L = length of the ultrasonic wave

 α = ultrasonic signal angle to the flow

The transit-time principle requires pipes to be full and have no bubbles and no particles.

Note: To transfer data to a computer, SOFT-PCE-TDS software is required. The software is sold separately - see accessories for details.

Each meter is assembled and calibrated by PCE Instruments in Germany. Therefore, a factory calibration certificate is provided by PCE Germany in the delivery contents of the meter. The certificate includes one measuring point on two different pipes. The reference display of the in-house test stand used by PCE for calibration has a valid DAkkS calibration certificate. This ensures traceability to the Physikalisch-Technische Bundesanstal (PTB) German national standard. Please note that because the meter's measured values depend upon the pipe geometry, material and coating; the medium type, temperature and speed; and the sensor type and measuring method, these parameters are listed on the supplied certificate for maximum traceability.

Subject to change

- ▶ Ideal for retrofitting
- ▶ Installation without process interruption
- ► Easy assembly
- ▶ Accurate and reliable
- ▶ No pressure loss
- ▶ Maintenance-free, no moving parts
- ▶ Wear-free
- ▶ Portable devices for control measurements

Subject to change

Specifications

Handheld measuring

range

Resolution 0.0001 m/s, 0.00033 ft/s Accuracy for DN \geq 50 ± 3.5% of measured value ± 1.0% of measured value mm:

for DN < 50 mm:

Reproducibility ± 1.0% of measured value

Media All liquids with an impurity <5% and a flow >0.03 m³/h

-32 ... 32 m/s, -105 ... 105 ft/s

Flow units Cubic meter [m³]

Liter [l]

Gallon (USA) [gal] Imperial gallon (UK) [igl] Million USA gallon [mgl]

Cubic foot [cf] Barrel (USA) [bal] Imperial barrel (UK) [ib]

Oil barrel [ob]

Time settings Per day [/d]

> Per hour [/h] Per minute [/m] And per second [/s]

Data logger 1800 measurements

Interface USB (for online measurement and reading of the

internal memory)

Protection IP 52

Power supply 3 x AA NiMH rechargeable battery / 2100-mAh (at full

> charge 12h running time) 100 ... 240V AC 50/60 Hz

Dimensions 214 x 104 x 40 mm / 8.4 x 4.1 x 1.5 in

Weight 450 g / 15 oz

Sensor (only PCE-TDS Nominal width DN 15 ... 100, 20 ... 108 mm /

100 HS) approx.3/4 ... 4"

Temperature of liquid -30 ... 160°C / -22 ... 320°F

Dimensions 45 x 30 x 30 mm / 1.7 x 1.1 x 1.1 in

Weight 75 g / < 1 lb

More information

Manual

Manual P1

Video Quick Start



Video



More product info



Similar products

